



SECTION-A-A




ELEVATION

PLAN VIEW




(FRONT) GAUGE
(BACK) GAUGE

GUIDE DETAIL (NON-WINDLOCK)



GUIDE DETAIL (WINDLOCK)



GUIDE DIMENSIONS

GUIDE TYPE	A	B	C	D	E	BETWEEN JAMB OPENING DEDUCTIONS = THEORETICAL "NEW" OPENING	
						TYPE	DEDUCT
2	5. 7/8"	3. 3/16"	4"	2. 9/16"	1. 1/4"	2	12"
3	6. 3/8"	3. 9/16"	4. 3/8"	2. 15/16"	1. 1/4"	3	12"
4	6. 3/4"	3. 15/16"	4. 3/4"	2. 3/4"	1. 1/4"	4	12. 3/4"
2(W/L)	6. 3/8"	3. 3/16"	4"	2. 9/16"	1. 1/2"	2(W/L)	12. 3/4"
3(W/L)	6. 3/8"	3. 9/16"	4. 3/8"	2. 15/16"	1. 1/2"	3(W/L)	12. 3/4"
4(W/L)	6. 3/4"	3. 15/16"	4. 3/4"	2. 3/4"	1. 1/2"	4(W/L)	13. 1/2"
5(W/L)	6. 3/4"	4"	4. 3/4"	2. 3/4"	1. 1/2"	5(W/L)	13. 1/2"
6(W/L)	8. 3/4"	6. 1/4"	7. 1/4"	3. 1/2"	1. 1/2"	6(W/L)	17. 1/2"

GENERAL NOTES

SLATS/HOOD: SELECT FINISH OPTION BELOW (HOOD INCLUDES WEATHER BAFFLE)

- ☐ GRAY POLYESTER TOP COAT
- ☐ WHITE POLYESTER TOP COAT

OTHER SURFACES:

- ☐ SHOP COAT BLACK PRIMER

OPERATION:

- ☐ RIGHT HAND SHOWN, LEFT HAND OPPOSITE

GUIDES:

- ☐ STRUCTURAL STEEL ANGLES OF 3/16" MINIMUM THICKNESS
- ☐ WITH PVC WEATHER SEAL

BOTTOM BAR:

- ☐ TWO 2"x2"x1/8" STEEL ANGLES WITH PVC BULB ASTRAGAL

MRK.	QTY.	OPENING SIZE		OPERATION	R.H.	CLEARANCES		OPTION	PROJECT:
		WIDTH "W"	HEIGHT "H"			L.H.	"X"		
									CONTRACTOR:
									DISTRIBUTOR:
									DATE:
									SHEET: OF: BY:

Richards-Wilcox

Garage Doors

ROLLTITE

5100 Timberlea Boulevard, Mississauga, ON Canada L4W 2S5

1-800-667-1572 • www.rwdoors.com

600 SERIES-INSULATED-BETWEEN JAMB (CHAIN HOIST)

Richards-Wilcox is not responsible for the use of improper installation procedures, structural supports as well as field inspection prior to manufacturing and installation.

APPROVAL SIGNATURE: _____ DATE: _____