

### 3M Fasara Decorative, Interior, and Privacy Performance Table

Fasara Type	Ultraviolet Rejected	Visible Light Transmitted	Visible Light Rejected	Solar Heat Reduction	Shading Coefficient 90 Degrees
<b>COMBINATION PATTERNS</b>					
Aerina	99%	Not more than 75%	Not Less than 12%	Not less than 10%	0.86
Illumina	199%	Not more than 49%	Not Less than 19%	Not less than 14%	0.62
<b>DOT PATTERNS</b>					
Aura 9	99%	Not more than 83%	Not Less than 8%	Not less than 7%	0.94
Cielo	99%	Not more than 45%	Not Less than 19%	Not less than 15%	0.69
Luna 6	99%	Not more than 44%	Not Less than 21%	Not less than 15%	0.67
Luna 9	99%	Not more than 39%	Not Less than 23%	Not less than 16%	0.63
Luna Cell	99%	Not more than 31%	Not Less than 24%	Not less than 17%	0.59
Luna Pico	99%	Not more than 32%	Not Less than 24%	Not less than 17%	0.60
Vista	99%	Not more than 69%	Not Less than 16%	Not less than 13%	0.80
<b>Line Patterns</b>					
Arpa	99%	Not more than 46%	Not Less than 22%	Not less than 17%	0.66
Fine	99%	Not more than 46%	Not Less than 25%	Not less than 19%	0.62
Lattice	99%	Not more than 34%	Not Less than 26%	Not less than 19%	0.60
Leise	99%	Not more than 74%	Not Less than 8%	Not less than 7%	0.94
Paracell	99%	Not more than 48%	Not Less than 19%	Not less than 15%	0.69
Pixela	99%	Not more than 57%	Not Less than 17%	Not less than 14%	0.75
Shutie	99%	Not more than 52%	Not Less than 21%	Not less than 17%	0.69
Slat	99%	Not more than 34%	Not Less than 26%	Not less than 19%	0.60
<b>Single Patterns</b>					
Altair	99%	Not more than 52%	Not Less than 16%	Not less than 12%	0.73
Charmonix	99%	Not more than 47%	Not Less than 29%	Not less than 20%	0.67
Fine Crystal	99%	Not more than 83%	Not Less than 8%	Not less than 7%	0.93
Lausanne	99%	Not more than 82%	Not Less than 9%	Not less than 8%	0.90
Luce	99%	Not more than 31%	Not Less than 25%	Not less than 17%	0.59
Matcrystal	99%	Not more than 85%	Not Less than 7%	Not less than 6%	0.92
Matcrystal i	99%	Not more than 83%	Not Less than 8%	Not less than 8%	0.91
Milano	99%	Not more than 59%	Not Less than 17%	Not less than 21%	0.75
Opaque White	99%	Not more than 6%	Not Less than 52%	Not less than 41%	0.29
Oslo	99%	Not more than 77%	Not Less than 9%	Not less than 8%	0.89
Rikyu	99%	Not more than 47%	Not Less than 18%	Not less than 13%	0.69
Sagano	99%	Not more than 53%	Not Less than 16%	Not less than 12%	0.75
San Marino	99%	Not more than 28%	Not Less than 27%	Not less than 42%	0.55
Vega	99%	Not more than 49%	Not Less than 16%	Not less than 12%	0.71
Yamato	99%	Not more than 52%	Not Less than 15%	Not less than 11%	0.75