

Laminating

GROUP

InKan Ltd. can laminate glass up to 2200mm x 4800mm (86"x189") using a wide range of interlayer's including DuPont SentryGlas (SGP) to Polyvinylbutyral (PVB) in clear and numerous colours.

Multi-ply laminates along with defect-free holes and notches as required by your custom project.

InKan Ltd. also recycle's PVB trimmings back into the marketplace to be used in other products.

Tempering

InKan Ltd. has two state of the art tempering furnace's capable of tempering glass up to 2400mm x 4800mm (95"x189")

Tempering available in 4mm, 5mm, 6mm, 8mm, 10mm, 12mm, 15mm and 19mm thicknesses. (5/32" - 3/4")

Certifications include CAN/CGSB 12.1-M90

ANSI Z97.1-2004

Heat Soak

InKan Limited is able to perform Heat Soak Test of Tempered Glass to EN 14179-1

Capable of testing glass from 4mm (3/16") to 19mm (3/4") thick in sizes up to 96" x 190"

InKan continues to be a leader in manufacturing with in house Heat Soak testing.

Custom Metal Fabricating

InKan Ltd. has been in the custom metal fabrication business since 1972.

InKan's custom metal shop can engineer, design and produce customized doors and frames,

revolving doors, balustrades and connections to support our customized glazing systems to

building structures, as well as heritage projects.

Our in-house equipment includes:

Brake Press, Shear, CNC Turret Punch along with a fully equipped machine shop with lathe, milling machine's

vertical and horizontal band-saw's, cutoff saw, aluminum cutting saws, welding equipment.

Our metal shop overhead crane allows InKan the capability to take on large projects



InKan Limited
14 Indell Lane, Brampton, Ontario, Canada L6T 3Y3
Tel:(905)793-4747 Toll Free:1 800 387-2481
Fax:(905)793-9367

www.inkan.ca


Email:info@inkan.ca











14 Indell Lane, Brampton, Ontario, Canada L6T 3Y3 Tel:(905)793-4747 Toll Free:1 800 387-2481

Fax:(905)793-9367 www.inkan.ca

Email:info@inkan.ca