



10. SLIDE IS PROVIDED WITH DETENT IN THE CLOSED POSITIONS.
9. SLIDE IS PROVIDED WITH SILENCING BUMPERS IN THE OPEN AND CLOSED POSITIONS.
8. LEFT HAND SLIDE SHOWN, RIGHT HAND SLIDE OPPOSITE.
7. HOLES OTHER THAN SHOWN MAY BE IN THE MEMBERS AT ACCURIDE OPTION.
6. FOR MOUNTING THROUGH SLIDE MEMBERS. MAX. .100 HIGH X .380 DIAMETER CLEARANCE NECESSARY IN ORDER TO CLEAR TRAVERSING BALL RETAINER.
5. WIDTH OF SLIDE MEASURED IN CLOSED POSITION, ACROSS THE AREA WHERE THE SLIDE MEMBERS ARE FULLY ENGAGED WITH BALL BEARINGS.
4. FINISH: ELECTRO-ZINC PLATED, CHROMATE COATED. (C=CLEAR ZINC, CB=BLACK ZINC)
3. LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
2. BALL BEARINGS: CARBURIZED STEEL.
1. MATERIAL: SLIDE MEMBERS AND COMPONENT PARTS: WORK-HARDENED, COLD-ROLLED STEEL.

NOTES: UNLESS OTHERWISE SPECIFIED

PART NUMBER -XX	LENGTH	TRAVEL	*A*	*B*	*C*	*D*	UNHANDLED RAIL 5740-XXXX	HANDED RAIL 7155-XXXX
4 4034-12	11.81 [300]	13.27 [337]	8.819 [224]	-	-	-	-1214-4E	-1214-4L -1214-4R
4 4034-14	13.78 [350]	15.21 [386]	8.819 [224]	-	-	-	-1214-4E	-1214-4L -1214-4R
4 4034-16	15.75 [400]	17.65 [448]	8.819 [224]	12.598 [320]	-	-	-1518-4E	-1518-4L -1518-4R
4 4034-17	16.73 [425]	18.15 [461]	8.819 [224]	12.598 [320]	-	-	-1518-4E	-1518-4L -1518-4R
4 4034-18	17.72 [450]	19.60 [498]	8.819 [224]	13.858 [352]	-	-	-1921-4E	-1921-4L -1921-4R
4 4034-19	18.70 [475]	20.09 [515]	8.819 [224]	13.858 [352]	-	-	-1921-4E	-1921-4L -1921-4R
4 4034-20	19.69 [500]	21.53 [547]	8.819 [224]	16.378 [416]	-	-	-2225-4E	-2225-4L -2225-4R
4 4034-22	21.65 [550]	23.45 [596]	8.819 [224]	13.858 [352]	17.637 [448]	18.898 [480]	-2225-4E	-2225-4L -2225-4R
4 4034-24	23.62 [600]	25.39 [645]	8.819 [224]	13.858 [352]	18.897 [480]	-	-2628-4E	-2628-4L -2628-4R
4 4034-26	25.59 [650]	27.33 [694]	8.819 [224]	13.858 [352]	21.417 [544]	-	-2628-4E	-2628-4L -2628-4R
4 4034-27	26.58 [675]	28.34 [720]	8.819 [224]	13.858 [352]	21.417 [544]	-	-2628-4E	-2628-4L -2628-4R
4 4034-28	27.56 [700]	29.27 [743]	8.819 [224]	13.858 [352]	21.417 [544]	23.937 [608]	-2628-4E	-2628-4L -2628-4R

THIS **Accuride** PRODUCT COVERED BY U.S. PATENTS #3205025, #3778120 AND OTHER U.S. PATENTS PENDING.

CUSTOMER: _____

P/N: _____ REV. _____

SCALE: _____ DATE: _____

CONTROLLING DOCUMENT
 ACCURIDE CUSTOMER

DRAWN: _____ TOLERANCES NOT SHOWN
 in mm in mm
 .xxx ± .010 .25 Travel ± .13 3.3
 .xx ± .030 .76 Holes ± .006 .15
 Angular ± .1°

APPROVED: _____ PART NUMBER: _____ REV. _____

THIS DOCUMENT IS FURNISHED FOR THE EXPRESS AND EXCLUSIVE PURPOSE OF CONVEYING INFORMATION TO CUSTOMERS AND SUPPLIERS OF ACCURIDE INTERNATIONAL, INC., AND IS NOT TO BE DISCLOSED TO COMPETITIVE SOURCES.