


BESAM VERSAMAX ICU
FULL BREAKOUT, TELESCOPIC EQUAL PANEL SINGLE
SLIDE DOOR SYSTEM WITH TRACKLESS
OR RECESSED TRACK GUIDE OPTIONS



NOTE:

THE STANDARD PACKAGE CONSISTS OF:

THE HEADER, FRAME, NARROW STILE DOOR(S) & SIDELITE(S),
PULL HANDLES, RECESSED FINGER PULL(S), GLASS STOPS & BLOCKS FOR 1/4" (6:3)
TEMPERED GLASS, BREAKAWAY, VERTICAL WEATHER-STRIPPING, HEAVY
DUTY FULL SIZE INDUSTRIAL CARRIER WHEELS AND TRACK ASSEMBLY,
CONCEALED HEAVY DUTY PIVOTS, TAMPER PROOF COVER LATCHES, FULL OPEN
DAMPENING DEVICE, FAST AND SLOW LEAF TIMING BELT ASSEMBLY, FLUSH BOLT
(FOR TRACKLESS W/ DOUBLE "C" HANDLES OR POSITIVE LATCH) AND
REPLACEMENT PARTS COMMON TO STANDARD DOOR LINE.

STANDARD FINISH: CLEAR - AA-M12C22A44, CLASS 1, .018 MM.
SPECIAL FINISHES ARE AVAILABLE.

OPTIONS:

MEDIUM STILE RAILS, POSITIVE LATCHING, BREAKOUT DAMPENER WITH 90° STOPS,
CONCEALED DOOR SWEEPS, 5/8", 1" & 1 1/4" INSULATED GLASS, FLUSHBOLT FOR
MIL LOCKING DOORS (FOR TRACKLESS W/ FINGER PULL, GUIDE TRACK OR
MIL RECESSED, SLOPED GLASS) - CLEAR OR ANODIZED, ENVIRONMENTAL, MOUNTING,
SELF CLOSING, DOUBLE "C" HANDLES, CLOSING DAMPENER, 1" WIDE JAMBS,
7" & 10" BOTTOM RAILS, ANTI-STATIC AND NURSE ASSIST MAGNETIC CATCHES.

DOOR PACKAGE WITH 1 3/4" JAMBS

MODEL NO.	CLEAR DOOR OPENING	OVERALL FRAME WIDTH	MASDRY OPENING WIDTH	ACTIVE & SIDELITE WIDTH
	A	B	C	D
ICU-TE-3FB0-8	53 11/16" (1363.6)	243 3/4" (618.4)	96 1/2" (2451.1)	32 9/16" (827.1)
ICU-TE-3FB0-10	69 11/16" (1770.1)	120" (3048.0)	120 1/2" (3060.7)	40 9/16" (1030.3)
ICU-TE-3FB0-12	85 11/16" (2176.5)	144" (3657.6)	144 1/2" (3670.3)	48 9/16" (1233.5)
KEY	2B/3-10 5/16" (676.3)	C - 1/2" (12.7)	B - 1/2" (12.7)	B/3 - 1/4" (14.3)


CONSULT FACTORY FOR ALL CUSTOM CONFIGURATION SIZES OR SIZES OVER 12'.

DOOR PACKAGE WITH 1" JAMBS

MODEL NO.	CLEAR DOOR OPENING	OVERALL FRAME WIDTH	MASONRY OPENING WIDTH	ACTIVE & SIDELITE WIDTH
	A	B	C 1/2"	D
ICU-TE-3FB0-8	54 11/16" (1389.0)	96" (2438.4)	96 1/2" (2451.1)	33 1/16" (839.8)
ICU-TE-3FB0-10	70 11/16" (1795.5)	120" (3048.0)	120 1/2" (3060.7)	41 1/16" (1043.0)
ICU-TE-3FB0-12	86 11/16" (2201.9)	144" (3657.6)	144 1/2" (3670.3)	49 1/16" (1246.2)
KEY	2B/3-5 5/16" (393.5)	C 1/2" (12.7)	B 1/2" (12.7)	B/3+1 (26.9)

CONSULT FACTORY FOR ALL CUSTOM CONFIGURATION SIZES OR SIZES OVER 12'.

SURFACE/RECESSED TRACK APPLICATIONS



L.H. SLIDE

VIEW FROM BREAK OUT SIDE

DOORS WILL BREAKOUT FROM ANY POSITION FOR
SURFACE & RECESSED TRACK APPLICATIONS

TRACKLESS APPLICATIONS

DOORS WILL ONLY BREAK OUT WHEN IN THE FULLY OPEN
POSITION FOR TRACKLESS APPLICATIONS

DWG NO. US23-3400-26											
DRN BY	SS	DATE	11/10/09	CHK BY	DW	DATE	11/10/09	REV.	H	DATE	5/29/14

ASSA ABLOY

NOTE: DRAWING IS DIMENSIONED IN BOTH ENGLISH AND METRIC.
REF. AS FOLLOWS: 1"(25.4). ALL METRIC SIZES ARE MILLIMETERS