

SPECIFICATIONS:


DOORS SHOWN AS FLEXIBLE VINYL TRAFFIC DOORS, DOUBLE ACTING, SHALL BE MODEL 100 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING _____ WIDE BY _____ HIGH.

VISION PANELS TO BE CONSTRUCTED OF 1/8" CLEAR POLYCARBONATE MATERIAL, INSTALLED ON THE EDGE OF EACH DOOR PANEL.
 15"x14" (STANDARD) AT 60" ON CENTER
 22"x22" (OPTIONAL) AT 64" ON CENTER

DOOR PANEL, BRACKET POCKET, TOP WIPER SEAL WINDOW FRAME, AND WEIGHT POCKET TO BE CONSTRUCTED OF 45oz. TWO-PLY VINYL COATED NYLON (USDA APPROVED). WEIGHTS ARE ADDED TO EACH PANEL (.117 PVC). NO IMPACT PLATES
 DOOR COLOR: FOREST GREEN

VALANCE OPTION:
 CONSTRUCTED OF 2-PLY 45oz. VINYL COATED NYLON ATTACHED TO .080 x 1 x 1 FOREST GREEN KYDEX ANGLE.
 WHEN HEIGHT IS MORE THAN 6", .120 VINLY WEIGHTS ARE ADDED TO VALANCE.

DOOR TO UTILIZE TOP MOUNTED GRAVITY-OPERATED HINGING SYSTEM, COMPLETE WITH 1/2" THICK ZINC WALL BRACKET WITH BEARINGS AND 5/8" DIAMETER STEEL ROD ARM.



OPTIONAL 100CRB HINGE

TOP MOUNTED GRAVITY HINGE

MODEL # 100, AIRGARD BIPARTING FLEXIBLE VINYL TRAFFIC DOOR			
@COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 1 800-543-4455 www.chasedoors.com	CUSTOMER INFORMATION:	DATE: 8/07/00 CHASE APPROVAL	
		FORM # SD4075	REV.