

SPECIFICATIONS:


DOORS SHOWN AS FLEXIBLE VINYL IMPACT TRAFFIC DOORS, DOUBLE ACTING, SHALL BE MODEL 300 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING _____ WIDE BY _____ HIGH.

DOOR SHALL BE CONSTRUCTED OF TWO LAYERS OF 2-PLY HEAVY DUTY BELTING (USDA APPROVED) WITH ANTI-ABRASION SURFACE, LAMINATED BACK-TO-BACK. BRACKET POCKET, BALLOON JAMB SEALS, AND TOP AND BOTTOM WIPER SEALS TO BE 45oz. TWO-PLY VINYL COATED NYLON. ALL PERIMETER EDGES TO BE HEAT SEALED TOGETHER.

DOOR TO UTILIZE TOP MOUNTED GRAVITY-OPERATED HINGING SYSTEM, COMPLETE WITH 1/2" THICK ZINC WALL BRACKET WITH BEARINGS AND 5/8" DIAMETER STEEL ROD ARM.
 OPTIONAL 100CRB HINGE

VISION PANELS TO BE CONSTRUCTED OF .160 CLEAR USDA FLEXIBLE PVC MATERIAL, INSTALLED ON THE EDGE OF THE DOOR PANEL.
 15"x14" (STANDARD) AT 60" ON CENTER
 22"x22" (OPTIONAL) AT 64" ON CENTER

VALANCE OPTION:
 WHEN HEIGHT IS LESS THAN 6".
 CONSTRUCTED OF 2-PLY VINYL COATED NYLON ATTACHED TO .080 x 1 x 1 FOREST GREEN KYDEX ANGLE.
 WHEN HEIGHT IS MORE THAN 6".
 CONSTRUCTED OF 2-PLY HEAVY DUTY BELTING ATTACHED TO 1/8" x 1 x 1 ALUMINUM ANGLE.



TOP MOUNTED GRAVITY HINGE

MODEL # 300, AIRGARD BIPARTING FLEXIBLE VINYL IMPACT TRAFFIC DOOR			
@COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 1 800-543-4455 www.chasedoors.com	CUSTOMER INFORMATION:	DATE: 7/25/00 CHASE APPROVAL	
		FORM # SD4011	REV. A