



**SPECIFICATIONS:**

DOORS SHOWN AS ALUMINUM SHEET STYLE SERVICE DOORS, DOUBLE ACTING, SHALL BE MODEL SD-2002 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING \_\_\_\_\_ WIDE BY \_\_\_\_\_ HIGH.

DOOR SHALL BE CONSTRUCTED OF .063" THICK ALUMINUM WITH HIGH-PRESSURE LAMINATE, BOTH SIDES.

SPECIFY COLOR AND NUMBER OF LAMINATE: \_\_\_\_\_

DOOR TO HAVE 1" THICK x 5" WIDE BACK EDGE REINFORCEMENT SPINE. BACK EDGE SPINE SHALL HAVE PLYWOOD CORE AND BE CLAD WITH PROPER ALUMINUM TO MATCH DOOR BODY.

COMPLETE WITH CHASE GRAVITY-OPERATED HINGING SYSTEM WITH HARDENED STEEL CAM AND ROLLER. BOTTOM HINGE PIN TO BE 1/2" DIAMETER STEEL MOUNTED TO 3/16" THICK STEEL ANGLE. TOP AND BOTTOM HINGES SHALL MOUNT DIRECTLY TO THE BACK EDGE SPINE.

OPTIONAL "E" SERIES HINGE

ACRYLIC VISION PANEL TO BE 1/4" TH. x 9" x 14" SET IN BLACK RUBBER MOLDING (STD).

INCLUDE OPTIONS AS INDICATED BELOW:

- 3-3/4"x8-3/4" HIGH ALUM. JAMB GUARDS
- 3-3/4"x12" HIGH ALUMINUM JAMB GUARDS
- 3-3/4"x18" HIGH ALUMINUM JAMB GUARDS

IMPACT PLATE (BOTH SIDES):  YES  NO

- STAINLESS STEEL IMPACT PLATES
- STAINLESS STEEL/GALVANIZED IMPACT PLATES
- GALVANIZED IMPACT PLATES
- PLASTIC IMPACT PLATES

(SPECIFY COLOR:)  FOREST GREEN  JADE  
 CADET BLUE  WHITE  GRAY  CLOUD GRAY  
 CHOCOLATE  RED  MEDIUM BROWN  NAVY  
 ROYAL BLUE  BLACK  BEIGE  BURGUNDY

IMPACT PLATE HEIGHT:

- 12"  18"  24"  36"  48"

BUMPER OPTIONS (BOTH SIDES ONLY):

- STANDARD TEARDROP CROSS-LINKED POLYETHYLENE (SPECIFY COLOR) \_\_\_\_\_ (AND HEIGHT) \_\_\_\_\_
- PVC STRIP (SPECIFY COLOR) \_\_\_\_\_  ALUM. STRIP (SPECIFY LOCATION) \_\_\_\_\_

MODEL # SD-2002, BIPARTING SHEET STYLE SERVICE DOOR			
@COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 1 800-543-4455 www.chasedoors.com	CUSTOMER INFORMATION:	DATE: 7/14/00	CHASE APPROVAL
		FORM # SD4121	REV. A