



NOTE:  
 DRAWINGS NOT TO SCALE  
 JAMB FRAMES MUST BE WITHIN ±1/8" OF FOS.

**SPECIFICATIONS:**

DOORS SHOWN AS POLYETHYLENE STYLE SERVICE DOORS, DOUBLE ACTING, SHALL BE MODEL SRP5000 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING \_\_\_\_\_ WIDE BY \_\_\_\_\_ HIGH.

DOOR SHALL BE CONSTRUCTED OF 1/2" THICK STRESS RELIEVED SANITIZED HIGH DENSITY POLYETHYLENE IN VARIOUS COLORS.  
 (SPECIFY COLOR:)  
 GRAY  BLACK  WHITE  
 RED  CHOC. BROWN  CLOUD GRAY  
 PANEL TO HAVE ALL EDGES FINISHED WITH RADIUS EDGE FOR SAFETY. BACK EDGE IS REINFORCED WITH A 1/4" THICK ANODIZED ALUMINUM EXTRUSION.

COMPLETE WITH CHASE GRAVITY-OPERATED HINGING SYSTEM WITH HARDENED STEEL CAM AND ROLLER. BOTTOM HINGE PIN TO BE 1/2" DIAMETER STEEL MOUNTED TO 3/16" THICK STEEL ANGLE. TOP HINGE SHALL MOUNT DIRECTLY THROUGH DOOR BODY. BOTTOM HINGE SHALL MOUNT DIRECTLY TO THE BACK EDGE SPINE.  
 'C' HINGE STANDARD  SRP5000 CAST ALUMINUM

ACRYLIC VISION PANEL TO BE 1/4" TH. x 9" x 14" SET IN BLACK RUBBER MOLDING (STD).

INCLUDE OPTIONS AS INDICATED BELOW:  
 5"x9" HIGH STEEL JAMB GUARDS

IMPACT PLATE (BOTH SIDES):  YES  NO  
 POLYETHYLENE IMPACT PLATES  
 (SPECIFY COLOR:)  
 GRAY  BLACK  
 WHITE  RED  BROWN  
 KYDEX IMPACT PLATES  
 (SPECIFY COLOR:)  
 FOREST GREEN  GRAY  
 CHOCOLATE  RED  MEDIUM BROWN  NAVY  
 ROYAL BLUE  BLACK  BEIGE  CLOUD GRAY  
 IMPACT PLATE HEIGHT:  
 12"  18"  24"  36"  48"

BUMPER OPTIONS (BOTH SIDES ONLY):  
 STANDARD TEARDROP CROSS-LINKED POLYETHYLENE (SPECIFY COLOR) \_\_\_\_\_ (AND HEIGHT) \_\_\_\_\_  
 PVC STRIP (SPECIFY COLOR) \_\_\_\_\_  ALUM. STRIP (SPECIFY LOCATION) \_\_\_\_\_

MODEL # SRP5000, BIPARTING PANEL SERVICE DOOR

@COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.  
 1 800-543-4455  
 www.chasedoors.com

CUSTOMER INFORMATION:

DATE:		CHASE APPROVAL	
FORM #		SD4167	REV. A