

QTY: \_\_\_\_\_ MODEL#: \_\_\_\_\_

COLOR: \_\_\_\_\_

FINISHED OPENING: \_\_\_\_\_

QUOTATION

ORDER

PO# \_\_\_\_\_

# DURULITE DOOR

## GASKETING

- FULLY GASKETED
- PARTIALLY GASKETED
- FRONT \_\_\_\_\_
- BACK \_\_\_\_\_
- BOTTOM \_\_\_\_\_

## FASTENERS FOR


- STEEL JAMB
- WOOD JAMB

## SEALS

- TOP SEAL
- EXTENDED \_\_\_\_\_ GAP
- UPPER HINGE SEAL
- LOWER HINGE SEAL

## OPTIONS

- 90° X 90° HARDWARE
- 180° X 90° HARDWARE
- SINGLE PANE WINDOW
- DOUBLE PANE WINDOW
- BUMPER \_\_\_\_\_ HIGH TEARDROP COLOR \_\_\_\_\_
- KICKPLATE \_\_\_\_\_ HIGH COLOR \_\_\_\_\_
- LOWER HINGE GUARD
- ROTO  ALUM  ST/STEEL
- SPRING ASSIST
- LOW-RISE
- NO-RISE
- HOLD OPEN
- WELD PLATES
- LOCKING DEVICE \_\_\_\_\_
- TOP/BOTTOM CANEBOLTS



# DUTCH DOOR

## GASKETING

- FULLY GASKETED
- PARTIALLY GASKETED

## FASTENERS FOR

- STEEL JAMB
- WOOD JAMB

- FRONT \_\_\_\_\_
- BACK \_\_\_\_\_

## SEALS

- UPPER HINGE SEAL
- DUTCH MIDDLE HINGE SEAL

## OPTIONS

- 90° X 90° HARDWARE
- 180° X 90° HARDWARE
- BUMPER \_\_\_\_\_ HIGH TEARDROP COLOR \_\_\_\_\_
- KICKPLATE \_\_\_\_\_ HIGH COLOR \_\_\_\_\_
- SPRING ASSIST
- LOW-RISE
- NO-RISE
- HOLD OPEN
- WELD PLATES
- LOCKING DEVICE \_\_\_\_\_

INDUSTRIAL DOORS WITH BUMPERS,  
SEE "POST-LOC.DXF" OR  
"POST-LOC.DWF" FOR RECOMMENDED  
OR REQUIRED POST LOCATIONS.

NOTES: \_\_\_\_\_

DRAWN BY \_\_\_\_\_ DATE \_\_\_\_\_

DRAWING NAME:  
SHOP-12.DWG

**Chase Doors**  
REDMOND DIVISION  
2809 SW 13th St. PO Box 577 • Redmond, Oregon 97756  
Phone:(800)547-6856 • Fax:(800)265-0126

TO: \_\_\_\_\_

JOB: \_\_\_\_\_

# DURULITE DUTCH DOOR WITH TRANSOM