



### Exterior Elevation



non-insulated section side view    insulated section side view




### Interior Elevation

height	sections
6'-3" to 8'-0"	4
8'-3" to 10'-0"	5
10'-3" to 12'-0"	6
12'-3" to 14'-0"	7
14'-3" to 16'-0"	8

width	panels
8'-0" to 9'-5"	2
9'-6" to 12'-11"	3
13'-0" to 16'-5"	4
16'-6" to 20'-2"	5
20'-3" to 24'-2"	6



- Panel Material:** 25 gauge commercial quality steel, hot dipped G60 galvanized.
- Color:** Exterior: White polyester top coat over primer. Interior: Gray polyester primer coat.
- Section Thickness:** 2"
- Panel Profile:** Two horizontal ribs with alternating 'v' grooves.
- Joint Design:** Tongue and groove rails.
- Stiles:** Box style, 18 gauge galvanized steel, full height of section. Riveted to inside rails and face of door.
- Insulation:**
  - (3220) None
  - (3221) CFC-free polystyrene with laminated vinyl backer. Average R-Value of 6.81; U-Value of 0.15
  - (3222) CFC-free polystyrene with steel backer. Average R-Value of 6.81; U-Value of 0.15
- Glazing (Optional):**
  - (3220) 24" x 6" x 1/8" DSB or Lexan  
24" x 12" x 1/8" DSB or Lexan  
Aluminum Full View White or Clear Anodized  
1/8" DSB glass, 1/8" Lexan, 1/4" Tempered glass
  - (3221/22) 24" x 6" x 3/4" Insulated glass  
24" x 12" x 3/4" Insulated glass  
34" x 16" x 3/4" Insulated glass  
(34" x 16" Not Available in End Panels on 10' and 14' Wide Doors)  
Aluminum Full View White or Clear Anodized  
1/8" DSB glass, 1/8" Lexan, 1/4" Tempered glass  
7/16" Insulated glass

05/2006 Copyright 2001 C.H.I. Overhead Doors

Door Qty.	Door Width	Door Height	Jamb Type	Model	Exterior Color

Miscellaneous Notes

**C.H.I. OVERHEAD DOORS**  
 1485 Sunrise Drive, Arthur, IL 61911  
 TOLL FREE: 800-677-2650 FAX: 217-543-3087

### C.H.I. 20 Gauge Commercial Ribbed Door

ARCHITECT:			
CONTRACTOR:			
PROJECT NAME:			
DOOR COMPANY:			
QUOTE NUMBER:		DOOR NUMBER:	
PREPARED BY:		DATE:	Page 1 of 2