


135° Internal Dogleg Corner



- A - 2-1/4", 2-5/8", 2-13/16", 3-5/8", 7-5/8"
- B - 5-5/8", 6-5/8", 7-5/8"
- C - 1-5/8", 2-5/8", 3-5/8"