



NOTE#1: Wood furring strips
to be Southern Pine PT
1"x3" nominal @ 16" o.c.

NOTE#2: Screw types
ITW Buildex screws, stainless steel
Wood screws, hot dipped galv.
Sheet metal screws, stainless steel.
Screw head to be for wood or metal only.
(see attached documentation for shear
and pullout test results)

NOTE#3: Panel adhesive to
be Liquid Nails, heavy duty
construction, LN901, applied
to furring strips, 3" diameter,
3/8" thick, every 16" o.c.

NOTE#4: Masonry Anchor type:
Model: PF3-134 ITW Ramset Red
Head, 3/16" x 1 3/4", with
1 1/4" embedment @ 6" from
top & bottom, and 12" o.c.

TYPICAL JOINT DETAIL
CLIP & CAULK ON BLOCK OR CONCRETE