

# Typical Gable Bracing



(1) 10d CC NAIL  
TOE-NAIL FROM TOP.

TOP CHORD BRACE LOCATION

(3) 10d CC NAILS  
TOE-NAIL TO TOP  
CHORD AT BACK SIDE

JA-5 CLIP (046027)  
@ ONE SIDE ONLY  
W/1 1/4" X 10 GA  
SHEAR NAILS:  
(6) @ FLANGE INTO TRUSS  
(3) @ FLANGE INTO BRACE

JA-5 ANGLE CLIP

INTERMEDIATE  
RAFTER

GABLE  
TRUSS

DIAGONAL GABLE END BRACE.  
LOCATE AT COLUMN OR VERTICAL  
STIFFENER.

ENDWALL  
COLUMN

BOTTOM  
CHORD

(4) 16d R.S.  
NAILS (TYP.)  
EA. MEMBER

BOTTOM CHORD BRACE LOCATION

## DIAGONAL GABLE BRACE

(4) 16D R.S. NAILS  
AT TRUSS TOP  
CHORD

2-PLY STIFFENER  
FASTEN WITH 2 ROWS  
10d CC AT 24" O.C.  
STAGGERED

24"

SEE FLOOR PLAN FOR  
SIZE AND LOCATIONS

STIFFENER WILL EXTEND  
TO HEADER OF DOOR  
OPENINGS IF APPLICABLE.

TRUSS BTM.  
CHORD

FALSE HEADER

(2) 10d CC  
EACH MEMBER

NOTCH STIFFENER  
FOR HEADER

OVERHEAD DOOR FALSE HEADER

PARTIAL HEIGHT SLIDING DOOR

TRUSS BTM.  
CHORD

TRACK BACKER

(2) 10d CC  
EACH MEMBER

(3) 10d CC  
EACH MEMBER

## VERTICAL END WALL STIFFENER