

ALUMINUM NO. PLATE

CONTINUOUS HINGE


ONE DBL. PRONG CEILING HOOK & TWO SGL. PRONG WALL HOOKS EA. OPG.

LOCK HOLE COVER PLATE


STAINLESS STEEL DEFIANT POCKET WITH PADLOCK EYE

14GA. DOOR & 16GA. FRAME

DOOR RECEIVES DIAMOND PERFORATIONS



ELEVATION



BOLT WELDED LOCKER UNITS TOGETHER @ 4 PLACES

16GA. TOP, BOTTOM, SHELF & DIVISIONS
DIVISION RECEIVES DIAMOND PERFORATIONS

18GA. BACK

72"

9"

72" HIGH SINGLE TIER ALL-WELDED DEFIANT LOCKER

12" & 15" WIDE, ALLOW 1/16" CREEPAGE PER FRAME

TYPICAL FOR 12", 15", 18" & 21" DEEP

SECTION @ WALL

This drawing shows a standard Penco Product. Any modifications to the product must be approved by Penco Engineering. 8/6/2001

