


ALUMINUM NO. PLATE
 ONE DBL. PRONG CEILING
 HOOK & THREE SGL. PRONG
 WALL HOOKS EA. OPENING

LOCK HOLE COVER PLATE
 STAINLESS STEEL RECESSED
 POCKET WITH PADLOCK EYE

14GA. DOOR & 16GA. FRAME
 DOOR RECEIVES DIAMOND
 PERFORATIONS



16GA. TOP, BOTTOM,
 SHELF & DIVISIONS
 DIVISION RECEIVES DIAMOND
 PERFORATIONS
 18GA. BACK

ELEVATION SECTION @ WALL
 72" HIGH DOUBLE TIER INVINCIBLE II KNOCKDOWN LOCKER

12" WIDE, ALLOW 1/16" CREEPAGE PER FRAME
 TYPICAL FOR 12", 15", 18", 21" & 24" DEEP

This drawing shows a standard Penco Product. Any modifications to the product must be approved by Penco Engineering. 8/6/2001

