



ALUMINUM NO. PLATE

ONE DBL. PRONG CEILING  
HOOK & THREE SGL. PRONG  
WALL HOOKS EA. OPG.

LOCK HOLE COVER PLATE

STAINLESS STEEL RECESSED  
POCKET WITH PADLOCK EYE

14GA. DOOR & 16GA. FRAME  
DOOR RECEIVES DIAMOND  
PERFORATIONS



16GA. TOP, BOTTOM,  
SHELF & DIVISIONS  
DIVISION RECEIVES DIAMOND  
PERFORATIONS  
18GA. BACK

ELEVATION

SECTION @ WALL

72" HIGH SINGLE TIER INVINCIBLE II KNOCKDOWN LOCKER

9" & 12" WIDE, ALLOW 1/16" CREEPAGE PER FRAME

TYPICAL FOR 12" & 15" DEEP

This drawing shows a standard Penco Product. Any modifications  
to the product must be approved by Penco Engineering. 8/6/2001



121272INV.dwg