

ALUMINUM NO. PLATE

SIX LOUVERS @ TOP
& BOTTOM EA. DOOR


ONE DBL. PRONG CEILING
HOOK & THREE SGL. PRONG
WALL HOOKS EA. OPG.

LOCK HOLE COVER PLATE

CHROME PLATED HANDLE
WITH PADLOCK EYE

16GA. DOOR & FRAME

DOOR NOT SHOWN



24GA. BODY &
TIER HEADS

ELEVATION

SECTION @ WALL

72" HIGH SINGLE TIER PENCO VANGUARD KNOCKDOWN LOCKER

TYPICAL FOR 9" & 12" WIDE, ALLOW 1/16" CREEPAGE PER FRAME

TYPICAL FOR 12" & 15" DEEP



121272V.dwg