


DB SERIES DOORS

DIMENSIONS IN () ARE METRIC.


TOP TO TOP
4 1/2" HINGES ONLY
1 3/4" DOOR



Consult factory for hardware locations not shown.

DIMENSIONS IN () ARE METRIC


A



Continuous or segmented 16 gauge reinforcement with provision for 4 1/2" x 4 1/2" full mortise template hinges

B


Continuous Welded Edge Seam



SPECIFIED CORE

D


Flush Top Continuous 16 Ga. Steel Channel




Steel Panel

12 Ga. Closer Reinforcement when specified


C



16 Ga. steel cylindrical lock reinforcement with provisions for Gov't Series 160 or 161 cylindrical lock sets (2-3/4" backset) and ANSI A115.2 lock front (1-1/8" x 2-1/4")



16 Ga. Mortise Lock reinforcement with provisions for Gov't Series 86 mortise lockset and ANSI A115.1 Lock Front (1-1/4" x 8)




Lever Lock Prep -161 DT (Modified 161 Prep) Conforms with the ANSI 115.18 161 lever lock Spec.

WARNING: Use ROSE TRIM with a minimum diameter of 3-5/16" to cover prep.

E

DOOR BOTTOM




Continuous 16 Ga. Steel Channel

Steel Panel

F

14 Ga. Astragal for Double Doors (opt.)



Inactive Leaf (Outside)

Beveled 1/8" in 2" (on lock side only)

CONSTRUCTION AVAILABLE
- 20, 18, OR 16 GAGE STEEL
- COLD ROLLED OR A-60 GALV STEEL
- HONEYCOMB CORE
- INSULATED CORE (POLYSTYRENE)
- TEMPERATURE RISE CORE
- TEXTURED STEEL

