



NOTES:

1. Exposed direct fastened panel
2. 32" panel coverage
3. 7/8" rib height, 2-2/3 center to center rib
4. Gauges: 26ga, 24ga
5. Applies over open framing or solid substrate
6. Finishes: MS Colorfast45, Kynar (PVDF) and Bare Galvalume

UNLESS OTHERWISE SPECIFIED ALL DIMS ARE IN INCHES AND INCLUDE APPLIED FINISH TOLERANCES		347 Coral Street, Santa Cruz, CA 95060	
MATL: N/A		TITLE: 7/8 CORRUGATED	
FINISH: N/A		DWG NO: PANEL_CORRUGATED	REV A
HARDNESS: --		SIZE: D	SCALE: 0.500
DRAWN BY: MDH			SHEET 1 OF 1