



NOTES:

1. Exposed fastened industrial panel for roof and wall applications
2. 36" panel coverage
3. 1-1/2" rib height at 7.2" centers
4. Gauges: 24ga and 26ga
5. Applies over open framing or solid substrate
6. Finishes: MS Colorfast45, Kynar 500 (PVDF) and Bare Galvalume

UNLESS OTHERWISE SPECIFIED ALL DIMS ARE IN INCHES AND INCLUDE APPLIED FINISH TOLERANCES		347 Coral Street Santa Cruz, CA 95060	
MATERIAL: N/A		TITLE: IC72	
FINISH: N/A		DWG NO: PANEL_IC72	
HARDNESS: --		REV A	
DRAWN BY: MDH		SIZE: D	SCALE: 0.500 SHEET 1 OF 1