



NOTES:

1. Direct fastened (exposed) panel
2. Applies over open framing or solid substrate
3. 32" panel coverage
4. 3" rib height
5. Trapezoidal rib on 8" centers
6. Gauge: 24ga
7. Finishes: Kynar 500 (PVDF), and Bare Galvalume

<small>UNLESS OTHERWISE SPECIFIED ALL DIMS ARE IN INCHES AND INCLUDE APPLIED FINISH TOLERANCES</small> <small>±.01 ±.03 ±.04 ±.05 ±.06 ±.07 ±.08 ±.09 ±.10 ±.12 ±.15 ±.20</small>	<small>347 Coral Street Santa Cruz, CA 95060</small>	
	<small>TITLE</small> T23	
<small>MATL:</small> N/A	<small>ENG NO</small>	
<small>FINISH:</small> N/A	<small>PANEL_T23</small>	<small>REV A</small>
<small>HARDNESS:</small> --	<small>SIZE D</small>	<small>SCALE 0.500</small>
<small>DRAWN BY:</small> MDH	<small>SHEET 1 OF 1</small>	