



- NOTES:
1. 180° F (82° C) MAXIMUM TEMPERATURE.
  2. POURABLE SEALER MUST CONTACT PRIMED QUICK APPLIED UNCURED EPDM FLASHING AND DECK MEMBRANE.
  3. POURABLE SEALER POCKET TO BE 1" (25 mm) MINIMUM FROM PENETRATION ON ANY SIDE.
  4. POURABLE SEALER MUST COMPLETELY FILL POURABLE SEALER POCKET TO PREVENT PONDING OF WATER.
  5. SECUREMENT IS REQUIRED FOR POURABLE SEALER POCKETS WHICH ARE GREATER THAN 18" (500 mm) IN DIAMETER. REFER TO SPECIFICATIONS.
  6. POURABLE SEALER TO BE MINIMUM 2" (50 mm) DEEP.
  7. ALL DEBRIS (PAINT, RUST, LEAD, OTHER FLASHINGS, ETC.) MUST BE REMOVED FROM THE PENETRATION.
  8. FOR ADDITIONAL INFORMATION, REFER TO POURABLE SEALER POCKET INSTALLATION INSTRUCTIONS IN THE MISCELLANEOUS SECTION.
  9. ON MECHANICALLY ATTACHED ROOFING SYSTEMS, ADDITIONAL MEMBRANE SECUREMENT IS REQUIRED. REFER TO SPECIFICATIONS.

PENETRATIONS, MEMBRANE, FLASHING AND METAL DAM (INSIDE POCKET) MUST BE PRIMED PRIOR TO APPLYING POURABLE SEALER.

C-16.6  
 QUICK APPLIED POURABLE SEALER POCKET

