



ITEM NO.	AW REV'S OPEN
01	

FDGF1

**GENERAL NOTES**

DESIGNED IAW U.L. SPECIFICATIONS FOR AUTOMATIC CLOSURE IN EVENT OF FIRE. CURTAIN IS 22 GA STEEL CROWN TYPE. ENDLOCKS ON EACH END OF EVERY OTHER SLAT. GUIDES ARE THREE ANGLE. HOODS ARE 24 GA GALVANIZED STEEL. SHOP COAT OF RUST INHIBITIVE PRIMER ON NONGALVANIZED STEEL SURFACES. ALL GALVANIZING PER ASTM. A-525 STANDARDS.

**NOTES**

CURTAIN FINISH : GALVANIZED STEEL  
BOTTOM BAR FINISH : GALVANIZED STEEL  
GUIDE FINISH : PRIMED STEEL  
HOOD(S) FINISH : GALVANIZED & PRIME STEEL  
OPTIONS ON THIS/THESE DOORS :

NOTE: THIS DRAWING IS INTENDED FOR EXAMPLE PURPOSES ONLY. DIMENSIONS WILL CHANGE WITH DOOR SIZE. CONSULT FACTORY FOR SPECIFIC DETAILS PER JOB.

**Wayne Dalton** Rolling Door Division

AKBAR 89 FIRE DOOR MODEL : FDGF1GS

PROJECT : **SAMPLE DRAWING**

NOTE: WIDTH **C** IS IMPORTANT AND MUST BE HELD

DOOR QTY.	ITEM NO.	HAND OF OPER.	CUST. OPG. NO.	WIDTHS			HEIGHTS				GUIDE		FOR BRACKET		SLAT LENGTH
				A	C	E	B	D	F	N	X	Y			
1	01	RH		9'0"	9'6-1/4"		9'0"	9'2"	10'6-1/2"	3-3/16"	16-1/2"	15"		9'4"	

ARCH :		
G.C. :		
DISTR :		
DISTR P.O. NO. :	PREPARED BY :	DATE : 12/11/95
QUOTE NUMBER	ORDER NUMBER	DWG. NO. OF

Target: Scale to fit 11x17  
AKBAR 89 FIRE DOOR