



Weather Shield®

Premium Wood & Aluminum Clad Windows & Doors

WEATHER SHIELD - ALUMINUM CLAD FRENCH SIDE HINGED DOOR INSWING WITH ADA SILL SIDE VIEW

SCALE: ELECTRONIC FILE IS FULL SCALE
REVISED 01/06

- INSWING FRENCH DOORS 8-0 AND TALLER CALL-OUT HEIGHTS ARE MANUFACTURED WITH A SHOOTBOLT AND SHOOTBOLT GROMMET AT HEAD JAMB (SHOWN) WHICH PROTRUDES THROUGH HEAD JAMB INTO ROUGH OPENING APPROXIMATELY 3/8" [10mm].
- SHOOTBOLT IS OPTIONAL FOR DOORS UP TO AND INCLUDING 7-2 HEIGHT DOORS.
- 7-1/2" [191mm] BOTTOM RAIL HEIGHT IS STANDARD ON 8-8, 8-10, 7-2, 8-0, AND 8-2 HEIGHT DOORS.
- 10" [254mm] BOTTOM RAIL HEIGHT IS STANDARD ON 9-0 AND 10-0 HEIGHT DOORS.
- 12" [305mm] BOTTOM RAIL HEIGHT IS AVAILABLE AS AN OPTION.
- WEATHER SHIELD RESERVES THE RIGHT, AS NECESSARY, TO CHANGE PRODUCT SPECIFICATIONS AND MATERIALS WITHOUT NOTICE.
- DIMENSIONS MAY BE ROUNDED TO THE NEAREST 1/16" [2mm].
- IMPORTANT: DIMENSIONS SHOWN ARE FOR STANDARD SHIM SPACE BETWEEN JAMB AND ROUGH OPENING WHEN INSTALLING IN A JURISDICTION NOT REQUIRING DESIGN PRESSURE-RATED PERFORMANCE. WHEN INSTALLING WINDOW/DOOR PRODUCTS IN A JURISDICTION REQUIRING PROJECTS TO BE INSTALLED IN THE SAME WAY THEY WERE INSTALLED FOR LABORATORY TESTING (TO MEET DESIGN PRESSURE PERFORMANCE), A SHIM SPACE, NOT TO EXCEED 1/4" [6mm], IS REQUIRED AROUND ENTIRE PERIMETER OF UNIT (EXCEPT AT DOOR SILL).

