



ProShield®
Premium Vinyl Clad Windows & Doors

SCALE: ELECTRONIC FILE IS FULL SCALE
(REVISED 2/07)

PROSHIELD - FRENCH SIDE HINGED DOOR OUTSWING WITH ADA SILL SIDE VIEW

- 8-0 CALL-OUT HEIGHT OUTSWING FRENCH DOORS ARE MANUFACTURED WITH A SHOOTBOLT AND SHOOTBOLT GROMMET AT HEAD JAMB (SHOWN) WHICH PROTRUDES THROUGH HEAD JAMB INTO ROUGH OPENING APPROXIMATELY 3/8" [10mm].
- SHOOTBOLT IS OPTIONAL FOR 6-8 AND 6-10 CALL-OUT HEIGHT DOORS.
- 7-1/2" [191mm] BOTTOM RAIL HEIGHT IS STANDARD ON ALL DOORS.
- 10" [254mm] AND 12" [305mm] BOTTOM RAIL HEIGHT IS AVAILABLE AS AN OPTION.
- WEATHER SHIELD RESERVES THE RIGHT, AS NECESSARY, TO CHANGE PRODUCT SPECIFICATIONS AND MATERIALS WITHOUT NOTICE.
- DIMENSIONS MAY BE ROUNDED TO THE NEAREST 1/16" [2mm].
- IMPORTANT: DIMENSIONS SHOWN ARE FOR STANDARD SHIM SPACE BETWEEN JAMB AND ROUGH OPENING. WHEN INSTALLING IN A JURISDICTION REQUIRING DESIGN PRESSURE (DP) RATED PERFORMANCE, WINDOW AND DOOR PRODUCTS MUST BE INSTALLED IN THE SAME METHOD THEY WERE INSTALLED FOR TESTING. A SHIM SPACE, NOT TO EXCEED 1/4" [6mm] IS REQUIRED AROUND THE SIDE JAMBS AND HEAD OF UNIT. REFER TO INSTALLATION INSTRUCTIONS FOR COMPLETE DETAILS.

