



NOTES:

1. LAP JOINTS AND SEAMS IN MEMBRANE SYSTEM A MINIMUM OF 2".
2. DOUBLE LAYER OF MEMBRANE MAY BE APPLIED TO THROUGH WALL FLASHINGS.
3. POST INSTALLATION DAMAGE TO THE MEMBRANE SHOULD BE REPAIRED WITH LIKE MATERIAL AND THICKNESS, EXTENDING AT LEAST 2" IN EACH DIRECTION OF THE DAMAGE, WITH 3M POLYURETHANE SEALANT 540, 3M POLYURETHANE CONSTRUCTION SEALANT 525 OR 3M AIR BARRIER 3015VP.
4. CONNECTION OF AIR AND VAPOR BARRIER FOR ROOF SYSTEM TO BE CONFIRMED WITH ROOF MANUFACTURER.
5. FOR ADDITIONAL QUESTIONS, PLEASE CALL 1-866-513-4026 OR VISIT WWW.3M.COM/CONSTRUCTION.

3M Air Barrier 3015VP

3M	SYSTEM: BRICK VENEER/STEEL STUD WALL	DATE: 05-23-16	DETAIL No: 3015VP-7.0A
	TITLE: DOOR HEAD DETAIL	SCALE: N.T.S.	
		DRAWN BY: JMB/APG	
THE DETAILS DEPICTED ABOVE ARE REPRESENTATIVE OF STANDARD CONDITIONS. MODIFICATIONS ARE REQUIRED FOR THE SPECIFIC INSTALLATIONS OF YOUR PROJECT, PLEASE CONTACT A TECHNICAL REPRESENTATIVE FOR ASSISTANCE.			