



1. CONTINUOUS STRUCTURAL ANGLE
2. INSULROCK BRAND INSULATING PANEL
3. 2" X THICKNESS X 2" X 16 GA. GALV. STEEL CHANNEL SEALED WITH SILICONE CAULK AND FASTENED TO BOTH PANEL FACINGS WITH #8 PAN HEAD TEK SCREWS SPACED 12" O.C.
4. #14 X LENGTH CORROSION RESISTANT SELF TAPPING TEK SCREW OR 1/4" DIA STAINLESS STEEL BOLT, LOCK WASHER, AND NUT, MIN. TWO PER PANEL OR AS REQUIRED.
5. 1/2" X 2 3/4" FIBER REINFORCED CEMENT SPLINE
6. ROOF INSULATION
7. SINGLE PLY ROOF MEMBRANE SEALED AND FASTENED TO EXTERIOR PANEL FACING IN ACCORDANCE WITH MEMBRANE MANUFACTURER'S INSTRUCTIONS
8. FILL ANY VOIDS WITH MINERAL WOOL
9. GRAVEL STOP AND FACIA