



ITEM ID	SIZE (INCH)	A	B (EST.)	C (EST.)	WEIGHT SCH 40 (lb)	WEIGHT SCH 10 (lb)
POWDER COATED						
7720P-XX	2	2-3/8 [60]	4 [102]	5-3/16 [132]	5.2	4.2
7725P-XX	2-1/2	2-7/8 [73]	4-1/4 [108]	5-11/16 [144]	6.8	4.9
7730P-XX	3	3-1/2 [89]	4-9/16 [116]	6-5/16 [160]	8.3	5.6
7740P-XX	4	4-1/2 [114]	5-1/16 [129]	7-5/16 [186]	10.8	6.7
7760P-XX	6	6-5/8 [168]	6-1/8 [156]	9-7/16 [240]	17.4	9.7
7780P-XX	8	8-5/8 [219]	7-1/8 [181]	11-7/16 [290]	25.1	13.2
HOT-DIPPED GALVANIZED						
7720G-XX	2	2-3/8 [60]	4 [102]	5-3/16 [132]	5.2	4.2
7725G-XX	2-1/2	2-7/8 [73]	4-1/4 [108]	5-11/16 [144]	6.8	4.9
7730G-XX	3	3-1/2 [89]	4-9/16 [116]	6-5/16 [160]	8.3	5.6
7740G-XX	4	4-1/2 [114]	5-1/16 [129]	7-5/16 [186]	10.8	6.7
7760G-XX	6	6-5/8 [168]	6-1/8 [156]	9-7/16 [240]	17.4	9.7
7780G-XX	8	8-5/8 [219]	7-1/8 [181]	11-7/16 [290]	25.1	13.2
XX = 40 OR 10 (SCH 40 OR SCH 10)						

- NOTES:
 1. FIELD INSTALL PLUG TO DESIRED ORIENTATION.
 2. SCH 40 PIPE IS CUT GROOVE. SCH 10 IS ROLLED.
 3. MADE IN AMERICA.



AGF Manufacturing, Inc.
 100 Quaker Lane
 Malvern, PA 19355
 Ph. 610-240-4900
 Fax 610-240-4906
 www.testandrain.com

DIMENSIONS ARE IN INCHES & [mm]

DRAWN	BFG	DATE	23OCT2015	SCALE	1:4
APPR'D	BFG	DATE	23NOV2015	WEIGHT	SEE TABLE
MATERIAL	VARIES				
PROJECT	REFERENCE DRAWING				

TITLE			CORRINSITE INLINE PIPE		
SIZE	DWG NO.	REV			
A	M7700	0			