




1/4-20 x 2.5 HWH BOLT & NUT
FIELD DRILL & INSTALL 1 @ HEAD.

#10 x 1 HWH SS TEK
ALTERNATE DIRECTION 16" O.C.
FIELD DRILLED AND INSTALLED



FLASHING OPTION



MODEL: K8204

SHEET: 1 OF 1