





 RECOMMENDED FOR MAINTENANCE.



REFER TO QUOTE FOR VISION WINDOW DETERMINED BY DOOR WIDTH & QUOTE)

- DRIVE SIDE  RIGHT  LEFT
- PANEL MATERIAL  VINYL 40OZ  2 PLY  ROLLTEX
- PANEL COLOR  \_\_\_\_\_
- WIND RIBS / WIND TABS  WIND RIBS  WIND TABS
- VISION OPTION  FULL WIDTH VISION SECTION  WINDOW (S) QTY. \_\_\_\_\_
- HOODS  NONE  ROLL COVER  ROLL AND MOTOR COVER  MATERIAL

- 208V  230V  460V  575V

- ACS100 - STEEL  ACS100 - STAINLESS STEEL

- PHOTO EYES  LIGHT CURTAINS

- MOTION DETECTOR  PULL CORD
- PUSH BUTTON  FLOOR LOOP
- \_\_\_\_\_
- \_\_\_\_\_

- HORN  RED
- AMBER STROBE  GREEN
- TRAFFIC LIGHT  LED SET

**RR300-RH DOOR - WITH COVER**

CONTROL PANEL:  
CONTROLS

CUSTOMER:		APPROVED BY:	
LOCATION:		APPROVED WITH CHANGES BY:	
SALESMAN / DEALER:		DATE:	SCALE = NTS
DESCRIPTION:			
<b>RR300 APPROVAL DRAWING</b>			
DRAWING NO:		DESIGNER:	DATE:
8300T0006		JT FISHER	12/05/2016

Rev	Change	Date	Name
A	ENCODER / TITLE	12/08/18	JTF
	BLOCK CHANGE		