



 RECOMMENDED FOR MAINTENANCE.


NOTE:
 A. FOR WINDOW CONFIGURATION AND QUANTITY REFER TO DOOR QUOTE.
 B. WIDTH GAUGE SUPPORT BRACKET ATTACHMENT MAY BE REQUIRED DEPENDING ON DOOR WIDTH.




LEFT VIEW



TOP VIEW



FRONT VIEW



SECTION A-A (NTS)

- DRIVE SIDE RIGHT LEFT
- SIDE COLUMN GALVANIZED
 RAL # _____
- SLAT COLOR ANODIZED CLEAR ALUMINUM
 RAL # _____
- INSULATED SLATS YES NO
- DISENGAGEMENT FRONT SIDE
 BOTH SIDES
- LOCKABLE DISENGAGEMENT YES NO
- HOOD FINISH GALVANIZED
 RAL # _____

- 208V 230V 480V 575V

- ACS100 - STEEL ACS100 - STAINLESS STEEL

- MOTION DETECTOR PULL CORD
- PUSH BUTTON FLOOR LOOP
- _____
- _____

- HORN RED
- AMBER STROBE GREEN
- TRAFFIC LIGHT LED SET

RR3000 / VISION - RH DOOR - WITH COVER
 CONTROL PANEL:
 CONTROLS

CUSTOMER:			APPROVED BY:		
LOCATION:			APPROVED WITH CHANGES BY:		
SALESMAN / DEALER:			DATE:	SCALE = NTS	
DESCRIPTION:					
RR3000 / VISION APPROVAL DRAWINGS					
DRAWING NO:		DESIGNER:		DATE:	
8300T0045		J. FISHER		12/28/2016	
Rev	Change	Date	Name		