





 RECOMMENDED FOR
MAINTENANCE.

NOTE:

- A. FOR WINDOW CONFIGURATION AND QUATITY REFER TO
DOOR QUOTE.
B. WIDTH GAUGE SUPPORT BRACKET ATTACHMENT MAY BE
REQUIRED DEPENDING ON DOOR WIDTH.



DRIVE SIDE	☐ RIGHT	☐ LEFT
SIDE COLUMN	☐ GALVANIZED	☐ RAL # _____
SLAT COLOR	☐ ANODIZED CLEAR ALUMINUM	☐ RAL # _____
INSULATED SLATS	☐ YES	☐ NO
DISENGAGEMENT	☐ FRONT SIDE	☐ BOTH SIDES
LOCKABLE DISENGAGEMENT	☐ YES	☐ NO
HOOD FINISH	☐ GALVANIZED	☐ RAL # _____

☐ 208V	☐ 230V	☐ 480V	☐ 575V
-------------------------------	-------------------------------	-------------------------------	-------------------------------

☐ ACS100 - STEEL	☐ ACS100 - STAINLESS STEEL
---	---

☐ MOTION DETECTOR	☐ PULL CORD
☐ PUSH BUTTON	☐ FLOOR LOOP
☐	☐
☐	☐

☐ HORN	☐ RED
☐ AMBER STROBE	☐ GREEN
☐ TRAFFIC LIGHT	☐ LED SET

RR3000 / VISION - LH DOOR - CHAIN DRIVE NO COVER
CONTROL PANEL:
CONTROLS

CUSTOMER:		APPROVED BY:	
LOCATION:		APPROVED WITH CHANGES BY:	
SALESMAN / DEALER:		DATE:	SCALE = NTS
DESCRIPTION:			
RR3000 / VISION APPROVAL DRAWINGS			
A	ENCODER / TITLE	12/08/18	JTF
Rev	Change	Date	Name
DRAWING NO:		DESIGNER:	DATE:
8300T0047		J. Fisher	12/27/2016