



## CONQUEST CLAPBOARD SIDING DOUBLE 4 1/2"



- A. INTERLOCKED PANEL WIDTH =  $9.000 \pm 0.030$
- B. BOTTOM PANEL WIDTH =  $4.500 \pm 0.030$
- C. CENTER BUTT HEIGHT =  $0.553 \pm 0.010$
- D. BOTTOM BUTT HEIGHT =  $0.511 \pm 0.020$
- E. BUTT HOOK LENGTH =  $0.440 \pm 0.030$
- F. PROFILE PANEL RADIUS =  $30.00 \pm 0.016$
- G. NAIL STRIP EDGE TO LOCK =  $0.625 \pm 0.030$
- H. NAIL SLOT CENTER LINE =  $0.250 \pm 0.030$
- J. NAIL SLOT HOLES =  $0.156 \times 1.010$
- K. END NOTCHING =  $2.000 \pm 0.125$
- L. LOCK HEIGHT =  $0.374 \pm 0.060$



WALL THICKNESS EXPOSED =  $.040 \pm .001$   
 WEIGHT PER FOOT - - - = .285 LBS.  
 OVERALL LENGTH - - - =  $12'-1" \pm 1/8"$   
 WARP - - - - - =  $.125"/\text{PANEL}$   
 WEEP HOLE - - - - - =  $.125"$   
 NAIL CENTER - - - - - =  $16"$

  
 First On America's Homes