



LANDSCAPE CLAPBOARD SIDING DOUBLE 4"



- A. INTERLOCKED PANEL WIDTH = 8.000 ± 0.030
- B. BOTTOM PANEL WIDTH = 4.000 ± 0.030
- C. CENTER BUTT HEIGHT = 0.533 ± 0.010
- D. BOTTOM BUTT HEIGHT = 0.496 ± 0.020
- E. BUTT HOOK LENGTH = 0.409 ± 0.030
- F. PROFILE PANEL RADIUS = 17.149 ± 0.016
- G. NAIL STRIP EDGE TO LOCK = 0.250 ± 0.030
- H. NAIL SLOT CENTER LINE TO CENTER LINE
= 0.350 ± 0.062
- I. NAIL SLOT HOLES = 0.150×1.010
- J. NAIL SLOT HOLES CTR. TO EDGE
= 0.250×0.030
- K. END NOTCHING = 1.312 ± 0.062
- L. END NOTCHING = 2.000 ± 0.062
- M. LOCK HEIGHT = 0.366 ± 0.010
- N. NAILHEM = 0.898 ± 0.030

WALL THICKNESS EXPOSED = $.040 \pm .001$
 WEIGHT PER FOOT - - - = .285 LBS.
 OVERALL LENGTH - - - = $12'-6" \pm 1/8"$
 WARP - - - - - = $.125"/\text{PANEL}$
 WEEP HOLE - - - - - = $.125"$
 NAIL CENTER - - - - - = $16"$




 First On America's Homes