



SENECA DUTCHLAP SIDING DOUBLE 4 1/2"



- A. INTERLOCKED PANEL WIDTH = 9.000 ± 0.030
- B. BOTTOM PANEL WIDTH = 4.500 ± 0.020
- C. CENTER BUTT HEIGHT = 0.553 ± 0.020
- D. BOTTOM BUTT HEIGHT = 0.511 ± 0.010
- E. BUTT HOOK LENGTH = 0.440 ± 0.030
- F. PROFILE PANEL RADIUS = 30.00 ± 0.016



- WALL THICKNESS EXPOSED = $.042 \pm .001$
- WEIGHT PER FOOT - - - = .310 LBS.
- OVERALL LENGTH - - - = $12'-6'' \pm 1/8''$
- WARP - - - - - = $.125''/\text{PANEL}$
- WEEP HOLE - - - - - = $.125''$
- NAIL CENTER - - - - - = 16"

Alside[®]
First On America's Homes