


DOUBLE FINISH TRIM



- A. 0.915 ± 0.030
- B. TOTAL THICKNESS = 0.792 ± 0.020
- C. EXPOSED WIDTH = 0.770 ± 0.020
- D. HOOK WIDTH = 0.205 ± 0.010
- E. SLOT WIDTH = 0.040 ± 0.010
- F. HOOK WIDTH = 0.340 ± 0.010
- G. SLOT WIDTH = 0.040 ± 0.010
- H. PANEL OFFSET = 0.180 ± 0.020
- J. TOTAL WIDTH = 1.450 ± 0.050

WALL THICKNESS EXPOSED = $.044 \pm .002$
 WEIGHT PER FOOT - - - = $.095$ LBS.
 OVERALL LENGTH - - - = $12'-6" \pm 1/8"$
 WARP - - - - - = $.500"/\text{PANEL}$
 WEEP HOLE - - - - - = N/A
 NAIL CENTER - - - - - = $16"$

