


## 1/2" J-CHANNEL



- A. SIDING POCKET WIDTH =  $0.500 \pm 0.020$
- B. SIDING POCKET DEPTH =  $0.750 \pm 0.040$
- C. TOTAL PROFILE THICKNESS =  $0.797 \pm 0.040$
- D. TOTAL PANEL WIDTH =  $1.500 \pm 0.050$
- E. ANGLE = 4 DEG.
- F. NAIL SLOT CENTER LINE =  $0.225 \pm 0.025$
- G. BEAD DEPTH =  $0.250 +0.020 -0.010$

WALL THICKNESS EXPOSED =  $.044 \pm .002$   
 WEIGHT PER FOOT - - - = .072 LBS.  
 OVERALL LENGTH - - - = 12'-6"  $\pm 1/8$ "  
 WEEP HOLE - - - - - = N/A  
 WARP - - - - - = 1"  
 NAIL CENTER - - - - - = 16"

**Alside**<sup>®</sup>  
 First On America's Homes