


5/8" J-CHANNEL



- A. SIDING POCKET WIDTH = 0.625 ± 0.020
- B. SIDING POCKET DEPTH = 0.760 ± 0.040
- C. TOTAL PROFILE THICKNESS = 0.910 ± 0.040
- D. TOTAL PANEL WIDTH = 1.450 ± 0.050
- E. ANGLE = 4 DEG.
- F. NAIL SLOT CENTER LINE = 0.225 ± 0.025
- G. BEAD DEPTH = $0.235 +0.020 -0.010$

WALL THICKNESS EXPOSED = $.044 \pm .002$
 WEIGHT PER FOOT - - - = .060 LBS.
 OVERALL LENGTH - - - = 12'-6" $\pm 1/8$ "
 WEEP HOLE - - - - - = N/A
 WARP - - - - - = 1"
 NAIL CENTER - - - - - = 16"

Alside[®]
 First On America's Homes