


SOFFIT CROWN MOLDING



- A. EXPOSED BEAD WIDTH = 0.305 ± 0.020
- B. SIDING POCKET DEPTH = 0.750 ± 0.020
- C. SIDING POCKET WIDTH = 0.788 ± 0.020
- D. TOTAL PANEL WIDTH = 3.700 ± 0.020
- E. NAILINGSTRIP WIDTH = 1.75 ± 0.020
- F. NAIL SLOT CENTER LINE = 0.225 ± 0.025

WALL THICKNESS EXPOSED = $.040 \pm .002$
 WEIGHT PER FOOT - - - = .165 LBS.
 OVERALL LENGTH - - - = $12'-6" \pm 1/8"$
 WEEP HOLE - - - - - = N/A
 WARP - - - - - = 1"
 NAIL CENTER - - - - - = 16"


 First On America's Homes