


RETROFIT STARTER STRIP



- A. 0.670 ± 0.015
- B. 0.530 ± 0.015
- C. 0.370 ± 0.010
- D. 0.840 ± 0.050
- E. 0.100 ± 0.010
- F. 1.220 ± 0.030
- G. 1.050 ± 0.015
- H. 2.135 ± 0.050

WALL THICKNESS EXPOSED = $.044 \pm .002$
 WEIGHT PER FOOT - - - = .115 LBS.
 OVERALL LENGTH - - - = $12'-6" \pm 1/8"$
 WEEP HOLE - - - - - = N/A
 WARP - - - - - = 1"
 NAIL CENTER - - - - - = 16"

