


BEADED CORNER STARTER



- A. 2.080 ± 0.025
- B. 0.460 ± 0.015
- C. 0.635 ± 0.010
- D. 0.100 ± 0.015
- E. 0.545 ± 0.015
- F. 0.825 ± 0.030
- G. 2.330 ± 0.030
- H. 0.375 ± 0.015
- J. 0.250 ± 0.030

WALL THICKNESS EXPOSED = $.044 \pm .002$
 WEIGHT PER FOOT - - - = .305 LBS.
 OVERALL LENGTH - - - = $20' \pm 1/4''$
 WARP - - - - - = 1"/PANEL
 WEEP HOLE - - - - - = N/A
 NAIL CENTER - - - - - = N/A

