


# FLUTED CORNER STARTER



- A. 1.260
- B. 2.060
- C. 0.635
- D. 0.100
- E. 0.545
- F. 0.825
- G. 2.400
- H. 0.375
- I. 0.250
- J. 0.340

WALL THICKNESS EXPOSED = .044 ± .002  
 WEIGHT PER FOOT — — — = .340 LBS.  
 OVERALL LENGTH — — — = 20' ± 1/4"  
 WEEP HOLE — — — — — = N/A  
 WARP — — — — — = 1"  
 NAIL CENTER — — — — — = N/A

