


3/4" INSIDE CORNER



- A. EXPODES BEAD = 1.500 ± 0.050
- B. SIDING POCKET = 0.750 ± 0.025
- C. POCKET DEPTH = 0.750 ± 0.050
- D. SIDING POCKET WIDTH = 0.900 ± 0.050
- E. NAIL SLOT CENTER = 0.313 ± 0.060
- F. NAILING STRIP WIDTH = 1.500 ± 0.050
- G. RADIUS = 2.000

WALL THICKNESS EXPOSED = $.044 \pm .002$
 WEIGHT PER FOOT - - - = .300 LBS.
 OVERALL LENGTH - - - = $10' \pm 1/4''$
 WARP - - - - - = $1/2''$ /PANEL
 WEEP HOLE - - - - - = N/A
 NAIL CENTER - - - - - = N/A

