


3/4" X 3.00" OUTSIDE CORNER POST



- A. TOTAL PANEL WIDTH = 3.000 ± 0.050
- B. EXPOSED BEAD WIDTH = 0.250 ± 0.040
- C. ANGLE = 90 DEG.
- D. SIDING POCKET WIDTH = 0.750 ± 0.040
- E. NAILING STRIP WIDTH = 2.000 ± 0.040
- F. SIDING POCKET DEPTH = 0.750 ± 0.040
- G. NAIL SLOT CENTER = 0.313 ± 0.062

WALL THICKNESS EXPOSED = $.048 \pm .002$
 WEIGHT PER FOOT - - - = .300 LBS.
 OVERALL LENGTH - - - = $10' \pm 1/4''$
 WEEP HOLE - - - - - = N/A
 WARP - - - - - = $1/2''$
 NAIL CENTER - - - - - = N/A

Alside®
 First On America's Homes