


## 3/4" X 4.00" OUTSIDE CORNER POST



- A. TOTAL PANEL WIDTH =  $4.000 \pm 0.050$
- B. EXPOSED BEAD WIDTH =  $0.250 \pm 0.040$
- C. ANGLE = 90 DEG.
- D. SIDING POCKET WIDTH =  $0.750 \pm 0.040$
- E. NAILING STRIP WIDTH =  $2.000 \pm 0.040$
- F. SIDING POCKET DEPTH =  $0.750 \pm 0.040$
- G. NAIL SLOT CENTER =  $0.313 \pm 0.062$

WALL THICKNESS EXPOSED =  $.048 \pm .002$   
 WEIGHT PER FOOT - - - = .300 LBS.  
 OVERALL LENGTH - - - =  $10' \pm 1/4''$   
 WEEP HOLE - - - - - = N/A  
 WARP - - - - - =  $1/2''$   
 NAIL CENTER - - - - - = N/A

**Alside**®  
 First On America's Homes