



SECTION A-A  
SUPPORT HANGER DETAIL

HEADROOM REQUIREMENTS	
DOOR HEIGHT	MINIMUM HEADROOM
7' - 12'	15-1/2"
13' - 18'	16-1/2"
19' - 20'	19-1/2"

\* ADD 4" FOR OPERATOR.

FLOOR TO SHAFT CENTER DISTANCE	
DRUM	FORMULA
D400-96	$F = DH + 12-1/4"$
D400-144	$F = DH + 12-1/4"$
D525-216	$F = DH + 12-5/8"$
D800-384	$F = DH + 14"$

DH = DOOR HEIGHT

STANDARD LIFT ANGLE MOUNT TRACK SET DETAIL