


SECTION A-A
SUPPORT HANGER DETAIL



HEADROOM REQUIREMENTS	
DOOR HEIGHT	MINIMUM HEADROOM
7' - 12'	15-1/2"
13' - 18'	16-1/2"
19' - 20'	19-1/2"

* ADD 4" FOR OPERATOR.

FLOOR TO SHAFT CENTER DISTANCE	
DRUM	FORMULA
D400-96	F = DH + 12-1/4"
D400-144	F = DH + 12-1/4"
D525-216	F = DH + 12-5/8"
D800-384	F = DH + 14"

DH = DOOR HEIGHT

NOTE: CONTACT ENGINEERING DEPARTMENT FOR HORIZONTAL TRACK PITCH CUTTING INSTRUCTIONS.

STANDARD LIFT FOLLOW THE ROOF PITCH
ANGLE MOUNT TRACK SET DETAIL