



SECTION A-A
SUPPORT HANGER DETAIL

| HEADROOM REQUIREMENTS | |
|-----------------------|------------------|
| DOOR HEIGHT | MINIMUM HEADROOM |
| 7' - 12' | 15-1/2" |
| 13' - 18' | 16-1/2" |
| 19' - 20' | 19-1/2" |

* ADD 4" FOR OPERATOR.

| FLOOR TO SHAFT CENTER DISTANCE | |
|--------------------------------|-----------------|
| DRUM | FORMULA |
| D400-96 | F= DH + 12-1/4" |
| D400-144 | F= DH + 12-1/4" |
| D525-216 | F= DH + 12-5/8" |
| D800-384 | F= DH + 14" |

DH = DOOR HEIGHT

NOTE: CONTACT ENGINEERING DEPARTMENT FOR HORIZONTAL TRACK PITCH CUTTING INSTRUCTIONS.

STANDARD LIFT FOLLOW THE ROOF PITCH
BRACKET MOUNT TRACK SET DETAIL