


EXPLODED VIEW



DOOR THICKNESS CHART:

- 1.75" THICK DOOR  
DOOR LEAFS DO NOT EXCEED 3'0"-7'0"  
MINIMUM JAMB DEPTH 6.625'
  
- 2.125" THICK DOOR  
DOOR LEAFS EXCEED 3'0"-7'0"  
DOOR LEAFS DO NOT EXCEED 4'0"-8'0"  
MINIMUM JAMB DEPTH 6.625'

LEGEND:

1. REINFORCED TORNADO RESISTANT STEEL DOORS.
2. TORNADO RESISTANT STEEL FRAME.
3. HEAVY DUTY TUBE & SCREW WALL ANCHORS.
4. REMOVABLE REINFORCED MULLION.

NOTES:

- A. SUPER HEAVY HINGES SHIPPED LOOSE.
- B. MULTI-POINT LOCK OR EXIT DEVICE.
- C. FIRE RATINGS AVAILABLE UP TO THREE HOURS ON 2.125" THICK DOORS ONLY.

